

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xRJ45 female/female + 1x3A fuse

- 1 × NEMA 1-15 (plug-solder connection)
- 1 × RJ45, 8-pole metal, CAT5e (female/female)
- 1 × fuse (3 A)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879452762
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	53 mm
Environmental characteristics Climatic	
Storage temperature min.	5 °C
Storage temperature max.	40 °C
Fuse	
Operating voltage AC	250 V

Operating voltage DC	32 V
Nominal current	3 A
Shielding plate	
Connection information	Threaded hole M4
Tightening torque	0,9 Nm
USA	
Connection geometry	4.8 x 0.5 mm
Operating voltage AC	125 V
Operating current	15 A
Connection	Plug-solder connection
No. of poles	2 + PE
Protection contact present	yes
RJ45	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector