

MODLINK MSDD DBL COMBI INSERT

USA 2XNEMA 5-15 GFCI + RJ45, without touch protection

- 2× NEMA-GFCI 5-15 (screw terminals)
- 1× RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27189217      |
| ECLASS-6.1            | 27189217      |
| ECLASS-7.0            | 27189217      |
| ECLASS-8.0            | 27189217      |
| ECLASS-9.0            | 27182806      |
| ECLASS-10.1           | 27182806      |
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ETIM-5.0              | EC000020      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879843737 |
| Packaging unit        | 1             |

Mechanical data | Mounting data

|        |        |
|--------|--------|
| Height | 88 mm  |
| Width  | 116 mm |
| Depth  | 72 mm  |

Environmental characteristics | Climatic

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -40 °C |
| Storage temperature max. | 70 °C  |

USA

|                               |       |
|-------------------------------|-------|
| Connection cross section max. | 6 mm² |
| AWG number max.               | 10    |

|                                       |                    |
|---------------------------------------|--------------------|
| Operating voltage AC                  | 125 V              |
| Operating current                     | 15 A               |
| Connection                            | Screw terminals SK |
| No. of poles                          | 2 + PE             |
| Connections per pole                  | 2                  |
| Protection contact present            | yes                |
| <b>RJ45</b>                           |                    |
| Operating voltage AC max. (UL-listed) | 30 V               |
| Operating voltage DC max. (UL-listed) | 42,4 V             |
| Current operating max. (UL)           | 175 mA             |
| Family construction form              | RJ45               |
| Family type Back side                 | RJ45               |
| Cable category min.                   | Cat5e              |
| Looking techniques                    | Snap-in connector  |