

MODLINK MSDD SINGLE COMBI INSERT BRAZIL

1x RJ45 + 3x data cutout

- 1x Brazil
- 1x RJ45, 8-pole metal, CAT6A (female/female)
- 3x RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879601153
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	87,5 mm
Width	50,7 mm
Depth	43 mm
Environmental characteristics Climatic	
Operating temperature min.	5 °C
Operating temperature max.	35 °C

Storage temperature min.	5 °C
Storage temperature max.	35 °C
Shielding plate	
Connection information	Threaded hole M4
Tightening torque	0,9 Nm
RJ45	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat6a
Looking techniques	Snap-in connector