

MODLINK MSDD SINGLE COMBI INSERT GERMANY ORANGE

2 x RJ45

1 x Germany (VDE) orange
2 x RJ45, 8-pole metal, CAT6A (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189234
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879848855
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	87,5 mm
Width	50,7 mm
Depth	43 mm
Environmental characteristics Climatic	
Operating temperature min.	-5 °C
Operating temperature max.	50 °C

Storage temperature min.	-10 °C
--------------------------	--------

Storage temperature max.	60 °C
--------------------------	-------

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque	0,9 Nm
-------------------	--------

Germany (VDE)

Connection cross section max.	2,5 mm²
-------------------------------	---------

AWG number max.	14
-----------------	----

Operating voltage AC	250 V
----------------------	-------

Operating current	16 A
-------------------	------

Connection	Spring clamp terminals FK
------------	---------------------------

No. of poles	2 + PE
--------------	--------

Connections per pole	2
----------------------	---

Protection contact present	yes
----------------------------	-----

RJ45

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42,4 V
---------------------------------------	--------

Current operating max. (UL)	175 mA
-----------------------------	--------

Family construction form	RJ45
--------------------------	------

Family type Back side	RJ45
-----------------------	------

Cable category min.	Cat6a
---------------------	-------

Looking techniques	Snap-in connector
--------------------	-------------------