**Modlink MSDD set contains:**

Frame 4000-68512-0000001

Art.No.: 4000-68512-4030001
Weight: 0.139 kg
Country of origin: CZ
Model designation: MSDD_1transparent_NEMA5-15Rlöt,RJ45Cat5e

## Link to Product

### Illustration




Product may differ from Image

### Commercial data

| | |
|---|---|
| URL webshop | https://shop.murrelektronik.com/4000-68512-4030001 |
| GTIN | 4048879691703 |
| EU-Customs tariff number | 85366990 |
| US-Customs tariff number | 8536694020 |
| ECLASS-6.0 | 27189234 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

| | |
|---|---|
| ECLASS-7.1 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-8.1 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-9.1 | 27189217 |
| ECLASS-10.0.1 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.0 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ECLASS-13.0 | 27182806 |
| ECLASS-14.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| ETIM-6.0 | EC002625 |
| ETIM-7.0 | EC002625 |
| ETIM-8.0 | EC002625 |
| ETIM-9.0 | EC002625 |
| ETIM-10.0 | EC002625 |
| customs tariff number | 85366990 |
| EAN | 4048879691703 |
| Packaging unit | 1 |
| **Frame** | |
| Housing | PA |
| Housing color | black |
| Cover | PC |
| Cover color | transparent |
| Suitable for installation wall thickness min. | 1 mm |
| Suitable for installation wall thickness max. | 5 mm |
| Degree of protection (EN IEC 60529) | IP65 |
| Operating temperature min. | -30 °C |
| Operating temperature max. | 70 °C |
| Storage temperature min. | -30 °C |
| **USA** | |
| Connection type | Plug-solder connection |
| No. of poles | 2 + PE |
| Protection contact present | Yes |
| Operating voltage AC | 125 V |
| Operating current | 15 A |
| **USB** | |
| USB specification | 3.0 |
| Locking techniques | Snap-in connector |
| Transmission rate max. | 5000 Mbit/s |
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating current | 1.5 A |
| Operating voltage AC max. (UL Listed) | 30 V |
| Operating voltage DC max. (UL Listed) | 42.4 V |
| **RJ45-5** | |
| Family construction form | RJ45 |
| Locking techniques | Snap-in connector |
| Cable category min. | Cat5e |
| Family type Back side | RJ45 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18

| | |
|---|---|
| Operating voltage AC max. (UL Listed) | 30 V |
| Operating voltage DC max. (UL Listed) | 42.4 V |
| Current operating max. (UL) | 175 mA |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-11-18