

## MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R KGM, Counter nut round M50/1,5

### [Link to Product](#)

| Commercial data                          |                     |
|------------------------------------------|---------------------|
| ECLASS-6.0                               | 27149109            |
| ECLASS-6.1                               | 27149109            |
| ECLASS-7.0                               | 27069219            |
| ECLASS-8.0                               | 27069219            |
| ECLASS-9.0                               | 27144424            |
| ECLASS-10.1                              | 27144424            |
| ECLASS-11.1                              | 27144424            |
| ECLASS-12.0                              | 27140801            |
| ETIM-5.0                                 | EC000211            |
| customs tariff number                    | 39269097            |
| GTIN                                     | 4048879031578       |
| Packaging unit                           | 1                   |
| Device protection   Electrical           |                     |
| Degree of protection (EN IEC 60529)      | IP65                |
| Mechanical data   Material data          |                     |
| Material housing                         | PA                  |
| Mechanical data   Mounting data          |                     |
| Mounting method                          | screwed, geschnappt |
| Sheet thickness min. (snap-on mounting)  | 1,5 mm              |
| Sheet thickness max. (snap-on mounting)  | 2 mm                |
| Sheet thickness min. (screw mounting)    | 1,5 mm              |
| Sheet thickness max. (screw mounting)    | 2 mm                |
| Height                                   | 8 mm                |
| Width                                    | 60 mm               |
| Depth                                    | 60 mm               |
| Environmental characteristics   Climatic |                     |
| Operating temperature min.               | -30 °C              |
| Operating temperature max.               | 70 °C               |