

MODLINK MSVD CABINET POWER OUTLETS

France (UTE) orange 250V AC / 16 A


France (UTE-NF) orange  
Screw terminals

Link to Product

Illustration



Product may differ from Image



Electrical data   Supply	
Operating voltage AC	250 V
Operating current min.	10 A
Operating current max.	16 A
Installation	
Connection cross section max.	2,5 mm²
AWG number max.	14
Installation   Connection	
Connection	Spring clamp terminals FK
Installation   Pin assignment	
Connections per pole	2
Mechanical data   Mounting data	
Mounting method	Snap-in connector
Suitable for mounting type	Mounting rail TH35
Height	68 mm
Width	47 mm
Depth	56 mm
Commercial data	
customs tariff number	85366990
GTIN	4048879031264
Packaging unit	1