

COMLIGHT57 LED GREEN STATUS LIGHT

Product discontinued

Compact status light
Flange M12 male, 4-pole
green

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ETIM-5.0	EC000232
customs tariff number	85318070
GTIN	4048879440141
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	23 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Material housing	Plastic
Mechanical data Mounting data	
Height	78,4 mm
Width	57 mm
Depth	57 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 3	BU 0 V
PIN 4	BK 24 V DC