

SIGNAL TOWER MODLIGHT30 EQUIPPED WITH LED MODULES

Green,amber,red with 4 pole M12 connection

Connection module + LED modules
green, yellow, red
with M12 connection
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
customs tariff number	85318070
GTIN	4048879496896
Packaging unit	1
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage DC	24 V
Current consumption max.	85 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Color housing	black

Material housing Plastic

Mechanical data | Mounting data

Height	30 mm
Width	30 mm
Depth	213 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 1	GN
PIN 2	RD
PIN 3	COM
PIN 4	YE