

Modlight50 Pro connecting modul base mounting

Input 24VDC

Base for floor mount
Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
customs tariff number	85319000
GTIN	4048879751551
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Color housing	black
---------------	-------

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	180 mm
--------	--------

Width	50 mm
-------	-------

Depth	50 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 1

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	9
--------------	---

PIN 1	LED-Modul RD
-------	--------------

PIN 2	LED-Modul YE
-------	--------------

PIN 3	LED-Modul GN
-------	--------------

PIN 4	LED-Modul BU
-------	--------------

PIN 5	LED-Modul CL
-------	--------------

PIN 6	Buzzer
-------	--------

PIN 7	24 V DC (0 V)
-------	---------------

PIN 8	Blinking
-------	----------

PIN 9	0 V (24 V DC)
-------	---------------