

COMLIGHT56 LED STATUS LIGHT

Multicolor, buzzer, IO-Link

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
customs tariff number	85319000
GTIN	4048879868440
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Nominal current	80 mA
Nominal rating	2 W

Industrial communication | IO-Link

IO-Link process data length output	1 Bytes
IO-Link process data length input	2 Bytes
IO-Link revision ID	V1.1
IO-Link type	Device

IO-Link cycle time min.	8 ms
IO-Link transmission rate	COM2 (38.4 kbit/s)
Port Class	A
Industrial communication HMI	
Buzzer volume	88 dB
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Material housing	PC
Mechanical data Mounting data	
Height	108,7 mm
Width	56 mm
Depth	56 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	75 °C
Connection type 1	
Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 1	BN 24 V DC (0 V)
PIN 3	BU 0 V (24 V DC)
PIN 4	BK IO-Link