

Modlight70 Pro LED modul red

Input 24VDC

LED module (red)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27371200
ECLASS-6.1	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ECLASS-10.1	27371220
ECLASS-11.1	27371220
ECLASS-12.0	27371220
ETIM-5.0	EC000232
customs tariff number	85319000
GTIN	4048879752626
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	62,5 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	PC
------------------	----

Mechanical data | Mounting data

Height	49 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C

Connection type 1

Mounting method	bayonet-locking
-----------------	-----------------