

Modlight70 Pro connecting modul IO-Link

Connection M12 4 pole, outlet bottom


Basic
with M12 connection
Outlet on the bottom
IO-Link V1.1
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
customs tariff number	85319000
GTIN	4048879832700
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V

Industrial communication | IO-Link

IO-Link process data length output	0 Bytes
IO-Link process data length input	6 Bytes
IO-Link revision ID	V1.1
IO-Link type	Device
IO-Link cycle time min.	8 ms
IO-Link transmission rate	COM2 (38.4 kbit/s)
Port Class	A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Color housing	black
Material housing	Plastic

Mechanical data | Mounting data

Height	140 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	50 °C
Storage temperature min.	-30 °C
Storage temperature max.	60 °C

Connection type 2

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 1	L +
PIN 2	n.c.
PIN 3	L -
PIN 4	C / Q
Mounting method	bayonet-locking