

SVS VALVE PLUG FORM B 10 MM FIELD-WIREABLE




230V LED+VDR PG9

Form B (10 mm)
230 V AC $\pm 10\%$
LED and RC
PG9

Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Side 1	
Degree of protection (EN IEC 60529)	IP65
Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ETIM-5.0	EC002062
customs tariff number	85366990

GTIN	4048879187237
------	---------------

Packaging unit	1
----------------	---

Electrical data

Capacity CX	15 ms
-------------	-------

Holding power max.	50 W
--------------------	------

Electrical data | Supply

Operating voltage AC	230 V
----------------------	-------

Operating voltage AC min.	207 V
---------------------------	-------

Operating voltage AC max.	253 V
---------------------------	-------

Cut-off peak voltage max.	450 V
---------------------------	-------

Current operating per contact max.	1 A
------------------------------------	-----

Current consumption max.	12 mA
--------------------------	-------

Diagnostics

Status indication LED	yellow
-----------------------	--------

Installation

Connection cross section max.	1,5 mm ²
-------------------------------	---------------------

Installation | Connection

Tightening torque	0,4 Nm
-------------------	--------

Mounting set	M3
--------------	----

Device protection | Electrical

Additional condition protection degree	inserted, locked, with screw connection
--	---

Mechanical data | Mounting data

Mounting method	PG9
-----------------	-----

Clamping range min.	6 mm
---------------------	------

Clamping range max.	8 mm
---------------------	------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------