

Bus terminating plug Desina Hybrid

DESINA® copper
for ECOFast®, DESINA®
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	19070403
ECLASS-6.1	19070403
ECLASS-7.0	19070403
ECLASS-8.0	19070403
ECLASS-9.0	27440190
ECLASS-10.1	27440190
ECLASS-11.1	27440190
ECLASS-12.0	27440190
ETIM-5.0	EC001855
customs tariff number	85366990
GTIN	4048879186766
Packaging unit	1
Industrial communication	
Data transmission rate max.	12 MBit/s
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Pollution Degree	2
Overvoltage category (EN 60950-1)	III
Mechanical data Material data	
Material housing	PC GF
Locking material	PA
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	50 °C
Important installation notes	

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.