



Adaptor M12 female 0° X-cod. / RJ45 90°

8-pol., shielded, CAT6A


Adapter
M12 – RJ45, top connection
Female straight – female 90°
8-pole
X-coded
Gigabit
Ethernet CAT6A
shielded
Cap nut

Link to Product

Illustration



Product may differ from Image



Side 1	
Family construction form	M12
Coding	X
Commercial data	
ECLASS-6.0	27143423
ECLASS-6.1	27279221
ECLASS-7.0	27440104

ECLASS-8.0	27440104
ECLASS-9.0	27440106
ECLASS-10.1	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ETIM-5.0	EC002640
customs tariff number	85366990
GTIN	4048879699419
Packaging unit	1

Electrical data | Supply

Operating current max.	1,75 A
------------------------	--------

Industrial communication

Supported protocol	Ethernet
Transfer parameters	CAT6A

Installation | Connection

Width across flats	SW18
--------------------	------