

EOL - MKDP 24/12 Cable entry plate

Product discontinued

Size 24
Cable diameter (12)× 8...12 mm

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27400569
ECLASS-11.1	27400569
ECLASS-12.0	27400569
ETIM-5.0	EC001855
customs tariff number	39269097
GTIN	4048879568524
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP66
Mechanical data Material data	
Material gasket	TPE
Material housing	PA
Mechanical data Mounting data	
Height	147,5 mm
Width	59,5 mm
Depth	25 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	100 °C
Conformities, approvals, certificates	
Combustibility class (UL94)	V-0