

MKDP 24/22 Cable entry plate

Product discontinued

Size 24
Cable diameter (16)× 3...6.5 mm, (4)× 5...9.2 mm, (2)× 8...12.5 mm

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27400569
ECLASS-11.1	27400569
ECLASS-12.0	27400569
ETIM-5.0	EC001855
customs tariff number	39269097
GTIN	4048879568579
Packaging unit	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP66
Mechanical data Material data	
Combustibility class (UL94)	V-0
Material gasket	TPE
Material housing	PA
Mechanical data Mounting data	
Height	147,5 mm
Width	59,5 mm
Depth	25 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	100 °C