**M12 male 0° / M12 female 0° A-cod. AIDA**

PUR 5x0.34 ye UL/CSA+drag ch. 10m

Art.No.: 7030-40041-1261000
Weight: 0.401 kg
Country of origin: DE
Model designation: MSBL0-A-U126_10.0-S30

**Advantages of our connectors:**

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available on request

If you are missing technical information? Please feel free to use our dictionary to find more technical details.

**Product details:**

AIDA conform
Male straight – female straight
M12 – M12, 5-pole
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.
Further cable lengths on request.

## Link to Product

**Illustration**




The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09


















Product may differ from Image

| | |
|---|---|
| Cable length | 10,00 m |
| **Side 1** | |
| Family construction form | M12 |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09

| | |
|---|---|
| No. of poles | 5 |
| Coding | A |
| Gender | male |
| Mounting method | inserted, screwed |
| Threaded hole | M12 x 1 |
| Tightening torque | 0,6 Nm |
| Width across flats | SW13 |
| Cable outlet | straight |
| suitable for corrugated tube (internal Ø) | 10 mm |
| Material contact | Copper alloy |
| Coating contact | gold plated |
| Degree of protection (EN IEC 60529) | IP67, IP66K, IP65 |
| **Side 2** | |
| Family construction form | M12 |
| No. of poles | 5 |
| Coding | A |
| Gender | female |
| Mounting method | inserted, screwed |
| Threaded hole | M12 x 1 |
| Tightening torque | 0,6 Nm |
| Width across flats | SW13 |
| Cable outlet | straight |
| suitable for corrugated tube (internal Ø) | 10 mm |
| Material contact | Copper alloy |
| Coating contact | gold plated |
| Degree of protection (EN IEC 60529) | IP67, IP66K, IP65 |
| **Commercial data** | |
| URL Webshop | https://shop.murrelektronik.com/7030-40041-1261000 |
| EU-Customs tariff number | 85444290 |
| US-Customs tariff number | 8544429090 |
| ETIM-9.0 | EC001855 |
| ETIM-10.0 | EC001855 |
| customs tariff number | 85444290 |
| EAN | 4048879620451 |
| Packaging unit | 1 |
| **Electrical data \| Supply** | |
| Operating voltage AC max. | 125 V |
| Operating voltage DC max. | 125 V |
| Current operating per contact max. | 4 A |
| **Device protection \| Electrical** | |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree | 3 |
| Rated surge voltage | 1,5 kV |
| Material group (IEC 60664-1) | I |
| **Mechanical data \| Material data** | |
| housing | PUR |
| Color housing | yellow |
| Color contact carrier | yellow |
| Screw connection | Zinc die-casting |
| Coating of fitting | Nickeled |
| Gasket | FKM |
| **Mechanical data \| Mounting data** | |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09

| | |
|---|---|
| Mounting method | inserted, screwed, Shaking protection |
| **Environmental characteristics \| Climatic** | |
| Operating temperature min. | -30 °C |
| Operating temperature max. | 85 °C |
| Additional condition temperature range | depending on cable quality |
| **Important installation notes** | |
| Note on bending radius | **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Note on strain relief | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |
| Note on mounting | Listed cables are developed see detail specification DIN EN 61076-2-101 with yellow injection part according to the AIDA coloration for cables in security applications., Any additional safety requirements are not explicitly taken into account and therefor |
| **Conformity** | |
| Product standard | EN IEC 61076-2-101 (M12) |
| **Installation \| Cable** | |
| Cable identification | 126 |
| Cable Type | 3 |
| Cable weigth | 38 g/m |
| UL AWM Style | 20549 / 10493 |
| Stranding | 1 × 5 wires around core filler twisted |
| Filler | Yes |
| Wire arrangement | BN, BK, BU, WH, GY |
| Material wire insulation | PP |
| Amount wires | 5 |
| Outer diameter insulation | 1.25 mm ± 0.05 mm |
| Conductor crosssection (wire) | 0,34 mm² |
| Material conductor wire | Stranded copper wire, bare |
| Core construction (wire) | 42 × 0.1 mm |
| Ingredient freeness wire insulation | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Material jacket | PUR |
| Outer-diameter (jacket) | 4.8 mm ± 5 % |
| Jacket Color | yellow / RAL 1021 |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Material property (jacket) | abrasion-resistant, low adhesion, good machinability, matte |
| Conductor resistance (wire) | 57 Ω/km @ 20 °C |
| Nominal voltage max. | 300 V |
| Withstand voltage (wire - wire) | 2.5 kV @ 60 s |
| Withstand voltage (wire - jacket) | 2.5 kV @ 60 s |
| Current load capacity max. (wire) | 4,5 A |
| Current load capacity (standard) | to DIN VDE 0298-4 |
| Operating temperature (static) | -40 °C … 80 °C / 90 °C @ 10000 h Operation |
| Operating temperature (dynamic) | -25 °C … 80 °C / 90 °C @ 10000 h Operation |
| Operating temperature (drag chain) | -25 °C … 80 °C / 90 °C @ 10000 h Operation |
| Flame resistance | UL 1581 § 1090, CSA FT2, IEC 60332-2-2 |
| Oil resistance | IEC 60811-404 |
| Chemical resistance | good |
| Other resistances | good resistance to gasoline, resistant to hydrolysis, resistant to microbes |
| Notes | application-related testing |
| Bending radius (fixed) | 5 × Outer diameter |
| Bending radius (dynamic) | 10 × Outer diameter |
| No. of bending cycles (C-track) | 10 Mio. @ 25 °C |
| Traversing distance (C-track) | 10 m @ 25 °C \| horizontal |
| Travel speed (C-track) | 3 m/s @ 25 °C |
| Acceleration (C-track) | 10 m/s² @ 25 °C |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09

| | |
|---|---|
| No. of torsion cycles | 5 Mio. |
| Torsion stress | ± 360 °/m |
| Torsion speed | 35 cycles/min |

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-09-09