

PE-Male module, 1-pole, axial screw t.

1000 V, 200 A


Male
PE
Axial screw connection
Technical data will be only guaranteed with Murrelektronik components.
Axial screw connection only for flexible wires
The clip 70MH-ZZ100-0000000 is needed (4×)

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27143424
ECLASS-7.0	27440209
ECLASS-8.0	27440209
ETIM-5.0	EC000438
customs tariff number	85366990
GTIN	4048879663939
Packaging unit	1

Electrical data | Supply

Operating current	200 A
-------------------	-------

Installation

Connection cross section min.	25 mm²
Connection cross section max.	70 mm²
AWG number min.	3
AWG number max.	0

Installation | Connection

Stripping length	16 mm
Wire insulation diameter variable max.	max. 12 mm (25 mm²); 16 mm (40 mm²)
Connection information	Axial screw connection
Tightening torque	(25...70 mm²); 9 Nm (70 mm²)
Tightening torque	8 Nm
Gender	male
Width across flats	SW5
Mating cycles min.	500

Installation Pin assignment	
No. of poles	PE
Device protection Electrical	
Pollution Degree	3
Mechanical data Material data	
Coating contact	silver-plated
Combustibility class (UL94)	V-0
Material housing	PC
Material contact	Brass
Mechanical data Mounting data	
Number of module slots	2
Height	61,1 mm
Width	34,3 mm
Depth	29,3 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C