

1,6 mm crimp contact m/turned/gold 0,14-0,37 mm²

100 Stück

Turned crimp contact
Male
1.6 mm
0.14...0.37 mm² (AWG 26...22)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879649933
Packaging unit	100

Installation

Connection cross section min.	0,14 mm²
Connection cross section max.	0,37 mm²
AWG number min.	26
AWG number max.	22

Installation | Connection

Stripping length	7 mm
Connection	Crimp
Gender	male
Mating cycles min.	500

Mechanical data | Material data

Coating contact	gold plated
Material contact	Brass
Mechanical data Mounting data	
Height	3,2 mm
Width	3,2 mm
Depth	25 mm