

1,6 mm crimp contact f/turned/gold/2,5 mm²

100 pieces

Turned crimp contact
Female
1.6 mm
2.5 mm² (AWG 14)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653602
Packaging unit	100
Installation	
Connection cross section max.	2,5 mm²
AWG number max.	14
Installation Connection	
Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	gold plated

Brass

Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com