

2,5 mm crimp contact f/turned/gold/2,5 mm²

100 pieces

Turned crimp contact
Female
2.5 mm
2.5 mm² (AWG 14)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653695
Packaging unit	100
Installation	
Connection cross section max.	2,5 mm²
AWG number max.	14
Installation Connection	
Stripping length	6,5 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	gold plated

Material contact Brass

Mechanical data | Mounting data

Height	4,5 mm
Width	4,5 mm
Depth	22 mm