

Male contact carriers 4-pole

Contact carrier
Male
4-pole
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261205
ECLASS-7.0	27440205
ECLASS-8.0	27440205
ECLASS-9.0	27440223
ECLASS-10.1	27440223
ECLASS-11.1	27440223
ECLASS-12.0	27440223
ETIM-5.0	EC000438
customs tariff number	85389099
GTIN	4048879649445
Packaging unit	1
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current	10 A
Industrial communication	
Data transmission rate max.	1000 MBit/s
Installation	
Connection cross section min.	0,14 mm²
Connection cross section max.	2,5 mm²
AWG number min.	26
AWG number max.	13
Installation Connection	
Wire insulation diameter min.	9,5 mm
Connection	Crimp

Gender	male
--------	------

Mating cycles min.	500
--------------------	-----

Installation | Pin assignment

No. of poles	4
--------------	---

Device protection | Electrical

Pollution Degree	3
------------------	---

Rated surge voltage	0,8 kV
---------------------	--------

Insulation resistance min.	100 MΩ
----------------------------	--------

Overvoltage category (EN 60664-1)	I
-----------------------------------	---

Overvoltage category (EN 60950-1)	III
-----------------------------------	-----

Mechanical data | Material data

Combustibility class (UL94)	V-0
-----------------------------	-----

Material housing	PA
------------------	----

Mechanical data | Mounting data

Height	20,3 mm
--------	---------

Width	16,7 mm
-------	---------

Depth	46 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	100 °C
----------------------------	--------

Climatic category (EN IEC 60068-1)	40/100/10
------------------------------------	-----------