

Pneumatic insert with valve - female, 1,6 mm

Pneumatic female  
Internal hose Ø  
1.6 mm  
Integrated valve  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

| Commercial data                          |               |
|------------------------------------------|---------------|
| ECLASS-6.0                               | 27261204      |
| ECLASS-6.1                               | 27261290      |
| ECLASS-7.0                               | 27440290      |
| ECLASS-8.0                               | 27440290      |
| ECLASS-9.0                               | 27440220      |
| ECLASS-10.1                              | 27440220      |
| ECLASS-11.1                              | 27440220      |
| ECLASS-12.0                              | 27440220      |
| ETIM-5.0                                 | EC000438      |
| customs tariff number                    | 39269097      |
| GTIN                                     | 4048879672825 |
| Packaging unit                           | 10            |
| Installation   Connection                |               |
| Gender                                   | female        |
| Mating cycles min.                       | 500           |
| Mechanical data                          |               |
| Operating pressure max.                  | 8 bar         |
| Integrated valve                         | yes           |
| Mechanical data   Material data          |               |
| Material housing                         | Delrin Acetal |
| Mechanical data   Mounting data          |               |
| Internal hose Ø                          | 1,6 mm        |
| Environmental characteristics   Climatic |               |
| Operating temperature min.               | -40 °C        |

Operating temperature max. 80 °C