

Power Supply Emparro20-Advanced-3-phase

IN: 3x400 - 500VAC; OUT: 70 - 85V/13,3ADC

The Emparro20-Advanced series of three-phase DIN rail power supplies are extremely versatile and are suitable for a wide range of applications where reliable DC power is required. The high efficiency of these power supplies allows you to save on energy costs while reducing your carbon footprint. Thanks to the low heat dissipation, the service life of the power supplies is extended and the cooling requirements of your control cabinet are reduced. The switching power supply also offers a 5-second power boost, which allows the operation of capacitive and inductive loads. With a very low inrush current, the input circuit breaker is prevented from tripping. The push-in terminal technology ensures quick and easy installation of the power supply unit. The powerful overvoltage protection effectively protects the power supplies from short-term voltage spikes, which extends the service life of the power supplies and increases machine availability.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044083
GTIN	4065909055298
Packaging unit	1
Electrical data	
Number of devices parallel connection max.	3
Number of devices series connection max.	20
Parallel connection	yes
Series connection	yes

Security level SELV/PELV

Electrical data | Input

Input voltage 1 AC	400 V
Input voltage 2 AC	500 V
Input voltage AC min.	350 V
Input voltage AC max.	575 V
Input current at input voltage 1 AC	1,6 A
Input current at input voltage 2 AC	1,3 A
Phase number input	3
Efficiency	96,3 % @ 400 V AC, 96,2 % @ 500 V AC

Electrical data | Output

Duration Power Boost max.	5 s
Output rating	960 W
Output voltage DC	72 V
Output voltage DC min.	70 V
Output voltage DC max.	85 V
Output current	21,3 A
Output current min.	17,1 A
Output current max.	21,3 A
Mains failure bridging time	20 ms
Power Boost	150 %
Ripple (s-s) max.	25 mV
Spikes (s-s) max.	40 mV

Diagnostics

Alarm contact yes

Installation | Connection

Connection Push-In spring clamp terminals

Device protection | Electrical

Installation height max. ASL	3000 m
Degree of protection (EN IEC 60529)	IP20
Protection class (EN IEC 61140)	I
Overload protection output	yes
Pollution Degree	2
Short-circuit protection output	yes
Overtemperature protection output	yes

Device protection | Mechanical

Cooling type Natural convection

Mechanical data | Material data

Combustibility class housing (UL94)	V-0
Conformal coated PCB	no
Material housing	Aluminium

Mechanical data | Mounting data

Net weight	1750 g
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-7.5/TH35-15
mounting position	horizontal, vertical
Height	129 mm
Width	100 mm
Depth	171,9 mm

Environmental characteristics | Climatic

Ambient temperature min.	-25 °C
Ambient temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Relative humidity max. (operation)	95 % no condensation

Environmental product conformity	
REACH	(EC) No 1907/2006
REACH-SVHC	compliant
RoHS	2011/65/EU
China RoHS	compliant EPUP 25
WEEE	compliant
Halogen-free-Material	JEDEC JS709A
Pb-free-Material	JESD97

Conformity	
CE	2014/30/EU

Approvals	
UL	E200364
SEMI F47	compliant