



MICO+ 48V DC 4.4 electronic circuit protection, 4-CANALS

IN: 48 V DC OUT: 48 V DC / 1-2-3-4 A

MICO+ 48 V DC 4.4
4 channels
Current adjustment 1, 2, 3, 4 A

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27141901
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-8.0	27371802
ECLASS-9.0	27371802
ECLASS-10.1	27371802

ECLASS-11.1	27371802
ECLASS-12.0	27371802
ETIM-5.0	EC001440
customs tariff number	85363010
GTIN	4048879402927
Packaging unit	1
Electrical data Input	
Input voltage DC	48 V
Input voltage DC min.	36 V
Input voltage DC max.	60 V
ON input voltage control inputs min.	20 V
ON input voltage control inputs max.	60 V
ON pulse length control inputs high min.	20 ms
Total current bridge set max.	40 A
Electrical data Output	
Switch-on capacity per channel max.	5 mF
Switching current max.	20 mA
Installation	
Connection cross-section inputs max.	16 mm ²
Connection cross-section outputs max.	1,5 mm ²
Connection cross-section control inputs / control outputs max.	2,5 mm ²
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	90 mm
Width	70 mm
Depth	80 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Connection type 10	
Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	48 V DC
Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	1
PIN 1	0 V
Family construction form	Bridging Contact
Gender	female
Color contact carrier	black
No. of poles	2
PIN 1	On
PIN 2	Off
Connection	Spring clamp terminals FK
Family construction form	terminal

Gender	female
Color contact carrier	green
No. of poles	1
PIN 1	0 V
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	1
PIN 1	48 V DC
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	Out 1
PIN 2	Out 1
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	Out 2
PIN 2	Out 2
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	Out 3
PIN 2	Out 3
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	Out 4
PIN 2	Out 4
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	On
PIN 2	Off
PIN 3	14
PIN 4	0.9