

MOTOR SUPPRESSOR

RC, 3x500VAC/4kW

3× 500 V AC +10%

RC

Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC000197
Classificação fiscal	85363010
GTIN	4048879019668

Quantidade por embalagem

1

Electrical data | Supply

Power frequency

50 ... 60 Hz

Electrical data | Input

Input voltage AC

500 V

Installation

Connection cross-section solid min.

0,75 mm²

Connection cross-section solid max.

2,5 mm²

Installation | Connection

Connection information

terminal

Family construction form

M4

Installation | Pin assignment

No. of poles

3

Device protection | Media

Flame resistance

flame retardant

Mechanical data | Material data

Combustibility class housing (UL94)

V-0

Material housing

Plastic

Material potting compound

2-component epoxy

Mechanical data | Mounting data

Height

75 mm

Width

45 mm

Depth

42 mm

Environmental characteristics | Climatic

Operating temperature min.

-20 °C

Operating temperature max.

60 °C