

ABB CONTACTOR SUPPRESSOR

Varistor, 24VDC



24 V AC/DC

VDR

For other configurations and voltages, please inquire.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-8.0	27371013
ECLASS-9.0	27371013
ECLASS-10.1	27371013

ECLASS-11.1	27371013
ECLASS-12.0	27371013
ETIM-5.0	EC002498
Classificação fiscal	85363010
GTIN	4048879018067
Quantidade por embalagem	1
Compatibility Compatible with	
Appropriate contactors	B 6, BC 6, KC 6, VB 6
Electrical data	
Damping factor	1.5× UN
Electrical data Input	
Input voltage AC min.	0 V
Input voltage AC max.	30 V
Input voltage DC min.	0 V
Input voltage DC max.	30 V
Installation Connection	
Connection information	self-securing cable forks
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Combustibility class housing (UL94)	V-0
Material housing	Plastic
Mechanical data Mounting data	
Height	20 mm
Width	11,5 mm
Depth	7,5 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C