

IMPACT67 COMPACT MODULE, PLASTIC

Ethercat, 8 dig. Out

Digital outputs  
DO8 - 2 A  
Ethernet 10/100 Mbit/s; M12, D-coded  
7/8", 5-pole, 2× max. 9 A  
M12, 5-pole, A-coded  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.  
mounting compatible with I/O modules of the MVK series

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais         |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27242604      |
| ECLASS-6.1               | 27242604      |
| ECLASS-7.0               | 27242604      |
| ECLASS-8.0               | 27242604      |
| ECLASS-9.0               | 27242604      |
| ECLASS-10.1              | 27242604      |
| ECLASS-11.1              | 27242604      |
| ECLASS-12.0              | 27242604      |
| ETIM-5.0                 | EC001599      |
| Classificação fiscal     | 85389099      |
| GTIN                     | 4048879051972 |
| Quantidade por embalagem | 1             |
| Electrical data   Supply |               |
| Total current UA max.    | 9 A           |
| Total current US max.    | 9 A           |
| Electrical data   Output |               |
| Overload resistant       | yes           |

|                                                 |                                  |
|-------------------------------------------------|----------------------------------|
| Short-circuit protected                         | yes                              |
| Output current per pin max.                     | 2 A                              |
| <b>Industrial communication   Bus data</b>      |                                  |
| Address setting type                            | Rotary switch, automatic         |
| <b>Diagnostics</b>                              |                                  |
| Diagnostic                                      | No voltage, Under voltage        |
| Diagnostic via BUS                              | per module and channel           |
| Diagnostic via LED                              | per module and channel           |
| LED display                                     | Ethernet connection/data traffic |
| <b>Device protection   Electrical</b>           |                                  |
| Degree of protection (EN IEC 60529)             | IP67                             |
| <b>Mechanical data   Mounting data</b>          |                                  |
| Suitable for mounting type                      | 2-hole screw mounting            |
| Height                                          | 39 mm                            |
| Width                                           | 63 mm                            |
| Depth                                           | 225 mm                           |
| <b>Environmental characteristics   Climatic</b> |                                  |
| Operating temperature min.                      | -25 °C                           |
| Operating temperature max.                      | 55 °C                            |
| Storage temperature min.                        | -25 °C                           |
| Storage temperature max.                        | 70 °C                            |
| <b>Connection type 5</b>                        |                                  |
| Connection type 1                               | 0, 2, 4, 6                       |
| Connection type 2                               | 1, 3, 5, 7                       |
| Connection type 3                               | Port1, Port2                     |
| Connection type 4                               | Power In                         |
| Connection type 5                               | Power Out                        |
| Family construction form                        | M12                              |
| Gender                                          | female                           |
| Color contact carrier                           | black                            |
| Coding                                          | A                                |
| No. of poles                                    | 5                                |
| PIN 1                                           | n.c.                             |
| PIN 2                                           | DO 01 03 05 07                   |
| PIN 3                                           | 0 V                              |
| PIN 4                                           | DO 00 02 04 06                   |
| PIN 5                                           | PE                               |
| Family construction form                        | M12                              |
| Gender                                          | female                           |
| Color contact carrier                           | black                            |
| Coding                                          | A                                |
| No. of poles                                    | 5                                |
| PIN 1                                           | n.c.                             |
| PIN 2                                           | n.c.                             |
| PIN 3                                           | 0 V                              |
| PIN 4                                           | DO 01 03 05 07                   |
| PIN 5                                           | PE                               |
| Mounting method                                 | inserted, screwed                |
| Tightening torque                               | 0,6 Nm                           |
| Family construction form                        | M12                              |
| Gender                                          | female                           |
| Color contact carrier                           | black                            |

|                          |              |
|--------------------------|--------------|
| Coding                   | D            |
| No. of poles             | 4            |
| PIN 1                    | TD +         |
| PIN 2                    | RD +         |
| PIN 3                    | TD -         |
| PIN 4                    | RD -         |
| Family construction form | 7/8"         |
| Gender                   | male         |
| Color contact carrier    | black        |
| No. of poles             | 5            |
| PIN 1                    | 0 V          |
| PIN 2                    | 0 V          |
| PIN 3                    | PE           |
| PIN 4                    | 24 V DC (US) |
| PIN 5                    | 24 V DC (UA) |
| Family construction form | 7/8"         |
| Gender                   | female       |
| Color contact carrier    | black        |
| No. of poles             | 5            |
| PIN 1                    | 0 V          |
| PIN 2                    | 0 V          |
| PIN 3                    | PE           |
| PIN 4                    | 24 V DC (US) |
| PIN 5                    | 24 V DC (UA) |