


MASI67 INSTALLATION TECHNOLOGY

Conversion from profile cable to 4xM12, 2x power


2x Aux. Power
MASI67 passive distribution box
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-8.0	27279219
ECLASS-9.0	27440108
ECLASS-10.1	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ETIM-5.0	EC001600
Classificação fiscal	85369010
GTIN	4048879048972
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage external DC min.	10 V
Operating voltage external DC max.	48 V
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	4000 mA
Total current max.	8 A
Device protection Electrical	

Degree of protection (EN IEC 60529) IP67

Mechanical data | Mounting data

Mounting method	screwed, geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	94 mm
Width	60 mm
Depth	39 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

Connection type 2

Connection type 1	Bus Out
Connection type 2	Bus Out
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	AS-i +
PIN 2	Aux Power 1 -
PIN 3	AS-i -
PIN 4	Aux Power 1 +
PIN 5	n.c.
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	AS-i +
PIN 2	Aux Power 2 -
PIN 3	AS-i -
PIN 4	Aux Power 2 +
PIN 5	n.c.