

TREE M-5TX IP67 Lite managed Switch 5 Ports




5x10/100BT IP67


5 port managed switch

5× M12 (female), D-coded

Supply PIN 1/3

Connection cables are in the online shop under "Connection Technology".

[Link do produto](#)**Ilustração**



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	19170106
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170401
ECLASS-10.1	19170401
ECLASS-11.1	19170401
ECLASS-12.0	19170401
ETIM-5.0	EC000734
Classificação fiscal	85176200
GTIN	4048879718301
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC min.	9,5 V
Operating voltage DC max.	31,5 V
Current consumption min.	97,5 mA
Current consumption max.	162,5 mA
Industrial communication	
Data transmission rate max.	100 MBit/s
Industrial communication Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
LLDP frames	forwarding
Ring topology	RSTP, STP
Switch type	managed
Industrial communication IIoT functions	
Webserver	HTTP, HTTPS
Switch Management	
Addressing	BOOTP/DHCP client, DCP, SSH-Befehlszeile
RSTP (IEEE 802.1D-2004, IEC 62439-1)	Default on

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 20/04/2024

Simple Network Management Protocol (SNMP) v1, v2c, v3 (default active)

VLAN managed (IEEE 802.1Q)	no
Time synchronization	NTP client

Diagnostics

Alarm contact	no
Diagnostic	No voltage
Remote maintenance	Open VPN client
LED display	Ethernet connection/data traffic
Port mirroring	1:1
RMON	yes
SNMP traps	yes
Syslog	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Invers-polarity protection	yes
Over voltage protection	yes

Mechanical data | Material data

Color housing	black
Material housing	Plastic

Mechanical data | Mounting data

Suitable for mounting type	3 hole screw mounting
Height	105 mm
Width	60 mm
Depth	40 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

Connection type 2

Connection type 1	4, 5
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	D
No. of poles	4
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	24 V DC (UB 1)
PIN 2	RD
PIN 3	0 V
PIN 4	TD
PIN 5	n.c.