

LED - LT 24/RED

(red)
24 V DC
with lamp test input
The modules are suitable for wall thickness of 1.5...5.0 mm.

[Link do produto](#)**Ilustração**

Produto pode diferir da imagem

Dados comerciais

ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
Classificação fiscal	85318070
GTIN	4048879041249
Quantidade por embalagem	10

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current consumption max.	10 mA

Installation | Connection

Connection information	Faston 2.8x0.8 mm
------------------------	-------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data

Diameter LED	5 mm
--------------	------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Diameter front panel drilling	9 mm
-------------------------------	------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	50 °C
----------------------------	-------