

MCS-B POWER SUPPLY 1-PHASE,

IN: 90-265VAC OUT: 24V/0,6ADC

INPUT: 90...265 V AC
OUTPUT: 24 V DC +3/-1%
Current: 0.6 A
Mains failure bridging min.
min. 25 ms (100 V AC); min. 150 ms (230 V AC)

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701

ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
Classificação fiscal	85044095
GTIN	4048879080392
Quantidade por embalagem	1
Electrical data	
Number of devices parallel connection max.	5
Number of devices series connection max.	2
Parallel connection	yes
Series connection	yes
Security level	SELV
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage 1 AC	100 V
Input voltage 2 AC	230 V
Input voltage AC min.	90 V
Input voltage AC max.	265 V
Input voltage DC min.	110 V
Input voltage DC max.	300 V
Input current at input voltage 1 AC	0,3 A
Input current at input voltage 2 AC	0,2 A
Inrush current max.	20 A
External back-up fuse per phase max.	10 A
Efficiency	81 % @ 100 V AC, 83 % @ 230 V AC
Electrical data Output	
Output voltage DC	24 V
Output voltage DC min.	22 V
Output voltage DC max.	28 V
Output voltage adjustable	yes
Output current	0,6 A
Ripple effective max.	50 mV
Spikes (s-s) max.	350 mV
Device protection Electrical	
Overload protection output	yes
Short-circuit protection output	yes
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	76 mm
Width	38 mm
Depth	87,5 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	50 °C
Derating from	50 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	5 %

Relative humidity max. (operation) 95 % no condensation

Connection type 2

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	-
PIN 2	+
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	PE
PIN 2	N
PIN 3	L