

MTS 1-PHASE SAFETY TRANSFORMER

P: 250VA IN: 230/400VAC +/- 15VAC OUT: 24VAC

Single-phase safety transformer  
250 VA  
Isolation class T 40/B  
Other voltages on request.

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais |          |
|------------------|----------|
| ECLASS-6.0       | 27031302 |
| ECLASS-6.1       | 27031302 |
| ECLASS-7.0       | 27031302 |
| ECLASS-8.0       | 27031302 |
| ECLASS-9.0       | 27031302 |
| ECLASS-10.1      | 27031302 |

|                          |               |
|--------------------------|---------------|
| ECLASS-11.1              | 27031302      |
| ECLASS-12.0              | 27031302      |
| ETIM-5.0                 | EC002486      |
| Classificação fiscal     | 85043180      |
| GTIN                     | 4048879078412 |
| Quantidade por embalagem | 1             |

**Electrical data**

|                |      |
|----------------|------|
| Security level | SELV |
|----------------|------|

**Electrical data | Supply**

|                 |              |
|-----------------|--------------|
| Power frequency | 50 ... 60 Hz |
|-----------------|--------------|

**Electrical data | Input**

|                                          |         |
|------------------------------------------|---------|
| Input voltage 1 AC                       | 230 V   |
| Input voltage 1 AC min.                  | 195,5 V |
| Input voltage 1 AC max.                  | 264,5 V |
| Input voltage 2 AC                       | 400 V   |
| Input voltage 2 AC min.                  | 340 V   |
| Input voltage 2 AC max.                  | 460 V   |
| Input current at input voltage 1 AC      | 1,35 A  |
| Input current at input voltage 2 AC      | 0,78 A  |
| Inrush current at input voltage 1        | 11,2 A  |
| Inrush current at input voltage 2        | 6,45 A  |
| Short-circuit current at input voltage 1 | 18,7 A  |
| Short-circuit current at input voltage 2 | 10,7 A  |

**Electrical data | Output**

|                           |        |
|---------------------------|--------|
| Output voltage AC         | 24 V   |
| Output voltage adjustable | no     |
| Power rating AC max.      | 250 VA |

**Device protection | Electrical**

|                                        |      |
|----------------------------------------|------|
| Insulation test voltage input - output | 4 kV |
|----------------------------------------|------|

**Mechanical data | Mounting data**

|                            |                                                    |
|----------------------------|----------------------------------------------------|
| Mounting method            | geschnappt                                         |
| Suitable for mounting type | Mounting rail TH35, Long-hole mounting, (EN 60715) |
| Mounting dimension a       | 86,5 mm                                            |
| Mounting dimension b       | 84 mm                                              |
| Mounting dimension c       | 4,8 mm                                             |
| Height                     | 102 mm                                             |
| Width                      | 96 mm                                              |
| Depth                      | 108 mm                                             |
| Diameter bore              | 4,8 mm                                             |
| Length bore                | 8,4 mm                                             |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 40 °C  |
| Storage temperature min.   | -40 °C |
| Storage temperature max.   | 80 °C  |

**Conformity**

|                  |                                                 |
|------------------|-------------------------------------------------|
| Product standard | EN 61558-2-4, EN 61558-2-6, EN 62041 category 0 |
|------------------|-------------------------------------------------|

**Connection type 3**

|                   |                    |
|-------------------|--------------------|
| Connection type 1 | Input              |
| Connection type 2 | Output             |
| Connection        | Screw terminals SK |

|                          |                    |
|--------------------------|--------------------|
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 5                  |
| PIN 1                    | + 15 V             |
| PIN 3                    | - 15 V             |
| PIN 4                    | 230 V              |
| PIN 5                    | 400 V              |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 2                  |
| PIN 2                    | 24 V DC            |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | metallic           |
| No. of poles             | 1                  |
| PIN 1                    | PE                 |