

Gateway Profibus-DP/AS-i, 2 Masters

Product discontinued since 2023-02-13


Gateway-Doublemaster
via pluggable spring clamp plug-in terminals on the front 0.5...1.5 mm²
AS-Interface/PROFIBUS DP
Specification 3.0
Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com
Other gateways on request.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
Classificação fiscal	85176200
GTIN	4048879046534
Quantidade por embalagem	1
Electrical data	
Rated operating current AS-Interface max.	200 mA
Electrical data Supply	
Operating voltage DC	30 V
Industrial communication Bus data	
Address range default setting	3

Address range min.	1
Address range max.	126
Address setting type	Buttons, PROFIBUS
Automatic baudrate detection	yes
Baud rate min.	9,6 kBaud
Baud rate max.	12 MBaud

Industrial communication | AS-Interface

AS-i specification	V3.0
Diagnostic interface serial	PS2/RS232
Cycle time AS-i	150 µs × (number of slaves + 2)

Industrial communication | Profibus

PROFIBUS function	Illustration of AS-Interface slaves as I/O process data in PROFIBUS DP, full diagnostic configuration via DP-master
-------------------	---

Installation | Connection

Family construction form	SUB-D9
--------------------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V

Mechanical data

Number of operating buttons	4
Function operating buttons	ESC, Mode, OK, Set

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	75 mm
Depth	83 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	85 °C

Conformity

Low Voltage Directive	EN 50295
-----------------------	----------