



MIRO 12.4 MULTI-TIMER

IN: 24 VAC/DC / 230 VAC - OUT: 230 VAC/DC / 6A

Relay output
Multitimer: 0.1...300
Spring clamp terminals

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27371790
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-8.0	27371605
ECLASS-9.0	27371605
ECLASS-10.1	27371605

ECLASS-11.1	27371605
ECLASS-12.0	27371605
ETIM-5.0	EC002538
Classificação fiscal	85364900
GTIN	4048879021890
Quantidade por embalagem	1

Electrical data | Input

Input voltage 1 AC	24 V
Input voltage 1 AC min.	20,4 V
Input voltage 1 AC max.	27,6 V
Input voltage 2 AC	220 V
Input voltage 2 AC min.	187 V
Input voltage 2 AC max.	253 V
Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	27,6 V
Input current	12 mA
Input current DC max.	12 mA
Control voltage AC	230 V
Control voltage AC min.	195,5 V
Control voltage AC max.	264,5 V
Control voltage DC	24 V

Electrical data | Output

Output voltage adjustable	no
Output current max.	6 A
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	230 V
Switching voltage DC max.	230 V
Switching current DC	8 mA

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	4,8 kV
Electrical lifetime	20000000 Cycles

Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	20 ms
Response time max.	8 ms
Bounce time max.	2 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C

Connection type 4

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	16
PIN 2	18
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	15
PIN 2	15
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	B 1
PIN 2	B 2
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	A 1
PIN 2	A 2