


MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: :24V/5ADC

Current: 5 A
Output rating: 120 W
with MES DIN-rail adapter
This power supply units meet the (EN 61000-3-2) standard for harmonic current.
Condensation not permitted

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701

ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
Classificação fiscal	85044095
GTIN	4048879065733
Quantidade por embalagem	1
Electrical data	
Security level	SELV
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Fuse protection 1 primary side external	1,6 A @230 V AC
Fuse protection 2 primary side external	1 A @400 V AC
Characteristic back-up fuse	Inertia
Input voltage 1 AC	230 V
Input voltage 1 AC min.	195,5 V
Input voltage 1 AC max.	264,5 V
Input voltage 2 AC	400 V
Input voltage 2 AC min.	340 V
Input voltage 2 AC max.	460 V
Input current at input voltage 1 AC	0,97 A
Input current at input voltage 2 AC	0,56 A
Electrical data Output	
Fuse protection secondary side external	10 A
Output suppression	LED, Screening capacitor, VDR
Output voltage DC	24 V
Output voltage adjustable	no
Output current max.	6 A
Type of secondary fuse	Flat fuse FKS
Ripple max.	5 %
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-15, Schlüssellochaufhängung, (EN 60715)
Mounting dimension a	75 mm
Mounting dimension b	84 mm
Mounting dimension c	5,8 mm
Height	95 mm
Width	69 mm
Depth	136 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Derating from	40 °C
Conformity	
Product standard	EN 61558-2-6, EN 62041 category I
EMC	EN 55011 B, EN 61000-3-2
Connection type 3	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female

Color contact carrier	metallic
No. of poles	1
PIN 1	PE
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	+
PIN 2	-
PIN 3	-
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	5
PIN 1	+ 15 V
PIN 3	- 15 V
PIN 4	230 V
PIN 5	400 V