

**Modlink MSDD-set: Frame 4000-68223-0000000,**  
insert 4000-68000-0010000 + 4000-68000-1700000

## Link do produto

### Ilustração



Produto pode diferir da imagem

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27189217      |
| ECLASS-6.1               | 27189217      |
| ECLASS-7.0               | 27189217      |
| ECLASS-8.0               | 27189217      |
| ECLASS-9.0               | 27189217      |
| ECLASS-10.1              | 27182806      |
| ECLASS-11.1              | 27182806      |
| ECLASS-12.0              | 27182806      |
| ETIM-5.0                 | EC002625      |
| Classificação fiscal     | 85389099      |
| GTIN                     | 4048879033176 |
| Quantidade por embalagem | 1             |

**Frame**

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Coating housing                               | surface finished      |
| Color cover                                   | transparent           |
| Material lid                                  | PC                    |
| Material housing                              | Fine zinc die casting |

**Shielding plate**

|                        |                  |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
| Tightening torque      | 0,9 Nm           |

**Germany (VDE)**

|                               |                    |
|-------------------------------|--------------------|
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 250 V              |
| Operating current             | 16 A               |
| Status indication LED         | yellow             |
| Connection                    | Screw terminals SK |
| No. of poles                  | 2 + PE             |
| Connections per pole          | 2                  |
| Protection contact present    | yes                |

**SUB-D9**

|                                       |        |
|---------------------------------------|--------|
| Operating voltage AC                  | 48 V   |
| Operating voltage DC                  | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Operating current                     | 3 A    |
| Current operating max. (UL)           | 175 mA |
| Family construction form              | SUB-D9 |
| Family type Back side                 | SUB-D9 |
| Gender                                | female |

|                    |                                                |
|--------------------|------------------------------------------------|
| Gender Rear        | male                                           |
| Looking techniques | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles       | 9                                              |

**SUB-D25**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D25                                        |
| Family type Back side                 | SUB-D25                                        |
| Gender                                | female                                         |
| Gender Rear                           | Lötanschluss                                   |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 25                                             |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |