

**Modlink MSDD-set: Frame 4000-68223-0000000,**  
insert 4000-68000-0230000 + 4000-68000-0030000

## Link do produto

### Ilustração



Produto pode diferir da imagem

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27189217      |
| ECLASS-6.1               | 27189217      |
| ECLASS-7.0               | 27189217      |
| ECLASS-8.0               | 27189217      |
| ECLASS-9.0               | 27189217      |
| ECLASS-10.1              | 27182806      |
| ECLASS-11.1              | 27182806      |
| ECLASS-12.0              | 27182806      |
| ETIM-5.0                 | EC002625      |
| Classificação fiscal     | 85389099      |
| GTIN                     | 4048879032766 |
| Quantidade por embalagem | 1             |

**Frame**

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Coating housing                               | surface finished      |
| Color cover                                   | transparent           |
| Material lid                                  | PC                    |
| Material housing                              | Fine zinc die casting |

**USA**

|                            |                        |
|----------------------------|------------------------|
| Connection geometry        | 4.8 x 0.5 mm           |
| Operating voltage AC       | 125 V                  |
| Operating current          | 15 A                   |
| Connection                 | Plug-solder connection |
| No. of poles               | 2 + PE                 |
| Protection contact present | yes                    |

**SUB-D9**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D9                                         |
| Family type Back side                 | SUB-D9                                         |
| Gender                                | female                                         |
| Gender Rear                           | Lötanschluss                                   |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9                                              |