



**Modlink MSDD-set: Frame 4000-68522-0000001,**  
insert 4000-68000-0140000 + 4000-68000-1200000

### Link do produto

#### Ilustração



Produto pode diferir da imagem

**Dados comerciais**

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27189217      |
| ECLASS-7.0               | 27189217      |
| ECLASS-8.0               | 27189217      |
| ECLASS-9.0               | 27189217      |
| ETIM-5.0                 | EC002625      |
| Classificação fiscal     | 85366990      |
| GTIN                     | 4048879538596 |
| Quantidade por embalagem | 1             |

**Frame**

|                                               |             |
|-----------------------------------------------|-------------|
| Degree of protection (EN IEC 60529)           | IP65        |
| Operating temperature min.                    | -30 °C      |
| Operating temperature max.                    | 70 °C       |
| Storage temperature min.                      | -30 °C      |
| Storage temperature max.                      | 80 °C       |
| Suitable for installation wall thickness min. | 1 mm        |
| Suitable for installation wall thickness max. | 5 mm        |
| Color cover                                   | transparent |
| Color housing                                 | black       |
| Material lid                                  | PC          |
| Material housing                              | PA          |

**Shielding plate**

|                        |                  |
|------------------------|------------------|
| Connection information | Threaded hole M4 |
| Tightening torque      | 0,9 Nm           |

**Germany (VDE)**

|                               |                           |
|-------------------------------|---------------------------|
| Connection cross section max. | 2,5 mm²                   |
| AWG number max.               | 14                        |
| Operating voltage AC          | 250 V                     |
| Operating current min.        | 10 A                      |
| Operating current max.        | 16 A                      |
| Connection                    | Spring clamp terminals FK |
| No. of poles                  | 2 + PE                    |
| Connections per pole          | 2                         |
| Protection contact present    | yes                       |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |