



Modlight Illumix Slim Line 32W


LED machine lamp, IP54, 24VDC, M8 connection

Modlight Illumix Slim Line
32 W

[Link do produto](#)

Ilustração





Produto pode diferir da imagem



Dados comerciais

ECLASS-6.0	27110306
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110345
ECLASS-10.1	27110345
ECLASS-11.1	27110345
ECLASS-12.0	27110345
ETIM-5.0	EC000348
Classificação fiscal	94054231
GTIN	4048879670777
Quantidade por embalagem	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	27,6 V
Power consumption max.	32 W

HMI | Illumination properties

Radiation angle min.	120 °
Luminous temperature	5500 K
Color reproduction (Ra) min.	80
Luminous efficacy	145 lm/W
Light color	daylight white
Luminous flux	4640 lm

Installation | Connection

Family construction form	M8
Gender	male

Installation | Pin assignment

Coding	A
No. of poles	4

Device protection | Electrical

Installation height max. ASL	2000 m
Degree of protection (EN IEC 60529)	IP54
Device protection Mechanical	
Shock resistance (EN IEC 60068-2-27)	50 g, 11 ms
Vibration resistance (EN IEC 60068-2-6)	10 mm (2 ... 9 Hz), 3 g (9 ... 200 Hz)
Mechanical data Material data	
Coating housing	eloxiert
Material housing	Aluminium
Material light cover	Diffuse polystyrene (PS)
Mechanical data Mounting data	
Height	34 mm
Width	1198 mm
Depth	24 mm
Screw head diameter max.	12 mm
Screw head thread max.	M5
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	50 °C
Relative humidity min. (operation)	5 %
Relative humidity max. (operation)	95 %
Connection type 1	
Family construction form	M8
Gender	male
Coding	A
No. of poles	4
PIN 1	n.c.
PIN 2	n.c.
PIN 3	0 V DC
PIN 4	24 V DC