

COMLIGHT56 LED RED STATUS LIGHT

Input 24VDC

Compact status light
red[Link do produto](#)**Ilustração**

Produto pode diferir da imagem

**Dados comerciais**

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
Classificação fiscal	85319000
GTIN	4048879853842
Quantidade por embalagem	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

Industrial communication | HMI

Luminous intensity	735 mcd
--------------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing Plastic

Mechanical data | Mounting data

Height	61 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)