

COMLIGHT56 LED GREEN STATUS LIGHT

Input 24VDC

Compact status light
green

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
Classificação fiscal	85319000
GTIN	4048879853866
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	26 mA
Industrial communication HMI	
Luminous intensity	1355 mcd
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	

Material housing Plastic

Mechanical data | Mounting data

Height	61 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)