

COMLIGHT56 LED RED STATUS LIGHT

With 4 pole M12 bottom exit

Compact status light
Flange M12 male, 4-pole
red

Link do produto**Ilustração**

Produto pode diferir da imagem

**Dados comerciais**

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
Classificação fiscal	85319000
GTIN	4048879855709
Quantidade por embalagem	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

Industrial communication | HMI

Luminous intensity	735 mcd
--------------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	78,8 mm
--------	---------

Width	56 mm
-------	-------

Depth	56 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
----------------------------	--------

Operating temperature max.	50 °C
----------------------------	-------

Connection type 1

Family construction form	M12
--------------------------	-----

Gender	male
--------	------

Coding	A
--------	---

No. of poles	4
--------------	---

PIN 3	BU 0 V (24 V DC)
-------	------------------

PIN 4	BK 24 V DC (0 V)
-------	------------------