

Signal tower Modlight70 Pro equipped with LED modules

white,blue,green ,red and buzzer, M12 plug downward

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
Classificação fiscal	85318070
GTIN	4048879825382
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	430 mA
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Height	334 mm

Width	70 mm
-------	-------

Depth	70 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	50 °C
----------------------------	-------

Storage temperature min.	-30 °C
--------------------------	--------

Storage temperature max.	60 °C
--------------------------	-------

Connection type 2

Family construction form	M12
--------------------------	-----

Gender	male
--------	------

Coding	A
--------	---

No. of poles	8
--------------	---

PIN 1	24 V DC (0 V)
-------	---------------

PIN 2	LED-Modul RD
-------	--------------

PIN 3	0 V (24 V DC)
-------	---------------

PIN 4	LED-Modul CL
-------	--------------

PIN 5	LED-Modul YE
-------	--------------

PIN 6	LED-Modul BU
-------	--------------

PIN 7	LED-Modul GN
-------	--------------

PIN 8	-
-------	---

Mounting method	bayonet-locking
-----------------	-----------------