




M12 male 90° A-cod. screw terminal

5-pol., max. 0,75mm², 6 - 8mm, shielded

Male 90°
M12, 5-pole
A-coded
shielded

Link do produto

Ilustração



Produto pode diferir da imagem

Side 1	
Family construction form	M12
Degree of protection (EN IEC 60529)	IP67
Dados comerciais	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116

ETIM-5.0	EC002635
Classificação fiscal	85366990
GTIN	4048879198813
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Installation	
Connection cross section max.	0,75 mm ²
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data Material data	
Coating housing	nickel plated
Material housing	Brass
Mechanical data Mounting data	
Clamping range min.	6 mm
Clamping range max.	8 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.