




Bus terminating plug M12 female B-cod.

Termination resistor, Profibus


PROFIBUS
Terminating resistor
Female
M12, 4-pole
B-coded

Link do produto

Ilustração



Produto pode diferir da imagem



Side 1	
Family construction form	M12
Degree of protection (EN IEC 60529)	IP67
Dados comerciais	
ECLASS-6.0	27061801
ECLASS-6.1	27260702

ECLASS-7.0	27440390
ECLASS-8.0	27440190
ECLASS-9.0	27440190
ECLASS-10.1	27440190
ECLASS-11.1	27440190
ECLASS-12.0	27440190
ETIM-5.0	EC001855
Classificação fiscal	85331000
GTIN	4048879419123
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC max.	30 V
Operating voltage DC max. (UL-listed)	30 V
Current operating per contact max.	4 A
Installation Connection	
Tightening torque	0,6 Nm
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data Material data	
Coating locking	Nickeled
Locking material	Zinc die-casting
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C