

SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE




110V/230V LED+RC PG9

Form A (18 mm)
110/230 V AC/DC
LED and RC
PG9

Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link do produto

Ilustração



Produto pode diferir da imagem

Side 1	
Degree of protection (EN IEC 60529)	IP65
Dados comerciais	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440105
ECLASS-11.1	27440105

ECLASS-12.0	27440105
ETIM-5.0	EC002062
Classificação fiscal	85366990
GTIN	4048879187572
Quantidade por embalagem	1

Electrical data | Supply

Operating voltage AC min.	110 V
Operating voltage AC max.	230 V
Operating voltage DC min.	110 V
Operating voltage DC max.	230 V
Current operating per contact max.	1 A

Installation | Connection

Tightening torque	0,4 Nm
Mounting set	M3

Installation | Pin assignment

No. of poles	2 + PE
--------------	--------

Device protection | Electrical

Additional condition protection degree	inserted, screwed
--	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.