


B24 frame (female) for 6 modules

a...f


B24
Frame
Female
for 6 modules
Technical data will be only guaranteed with Murrelektronik components.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais

ECLASS-6.0	27143424
ECLASS-6.1	27261209
ECLASS-7.0	27440206
ECLASS-8.0	27440206
ECLASS-9.0	27440206
ECLASS-10.1	27440206
ECLASS-11.1	27440206
ECLASS-12.0	27440206
ETIM-5.0	EC002312
Classificação fiscal	85389099
GTIN	4048879641814
Quantidade por embalagem	1

Installation

Connection cross section min.	1 mm ²
Connection cross section max.	6 mm ²
AWG number min.	18
AWG number max.	10

Installation | Connection

Connection	Screw terminals SK
Insertion cycles safety element min.	20
Mating cycles min.	500

Installation | Pin assignment

No. of poles	2 + PE
--------------	--------

Mechanical data

Holding force modules (insert) min.	300 N
Holding force modules (pull) min.	600 N
Holding force PE contact	250 N
Frame type	female
Pulling force max.	60 N

Mechanical data | Material data

Coating housing	nickel plated
Coating contact	nickel plated
Combustibility class (UL94)	V-0
Material housing	Zinc die-casting
Material contact	Brass
Material safety element	PC GF

Mechanical data | Mounting data

Number of module slots	6
Size	B24
Height	36,5 mm
Width	34,4 mm
Depth	111,2 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10